

Lamp with magnifying glass LAMP-5D-LEDN1

Instructions of use

Safety

Improper use of the lamp can cause its damage, electric shock, injuries or death.

During work with the use of the lamp it is necessary to obey safety regulations which apply to a workplace.

Repairs should be carried out by a qualified service centre with the use of proper spare parts.

Specifications

Power supply: 220-240V/50Hz

Power consumption: 8W

Light source: 80 diodes

Power supply cord: 2-wire, length approx. 1,4 m

Magnification: 5 dioptries

Operation

Fix the lamp holder to an edge of a table.

Insert the lamp to the holder.

Connect the lamp to the power source.