



OSV3XME3E1E

Ver.a.0


■Features

- Highest Luminous Flux
- · Super Energy Efficiency
- · Long Lifetime Operation
- Superior ESD protection
- Superior UV Resistance

■Applications

- · Money Detector
- · UV-Curing
- · Sensor light
- · Photo-catalyst
- · Other Lighting


■Outline Dimension



■Absolute Maximum Rating

Item	Symbol	Value	Unit
DC Forward Current	I_{F}	700	mA
Pulse Forward Current*	I_{FP}	1,000	mA
Reverse Voltage	V_R	5	V
Power Dissipation	P_{D}	3,150	mW
Operating Temperature	Topr	-30 ~ +85	$^{\circ}\!\mathbb{C}$
Storage Temperature	Tstg	-40~ +100	$^{\circ}\!\mathbb{C}$
Lead Soldering Temperature	Tsol	260°C /5sec	-

■Directivity



■Electrical -Optical Characteristics (Ta=25°C)

Item	Symbol	Condition	Min.	Тур.	Max.	Unit
DC Forward Voltage	V_{F}	I _F =350mA	3.0	3.3	4.0	V
	VF	I _F =700mA	3.5	3.8	4.5	V
DC Reverse Current	I_R	V _R =5V	-	-	10	μΑ
Peak Wavelength	$\lambda_{ m P}$	I _F =700mA	380	385	390	nm
Radiant Power	Ро	I _F =700mA	550	600	-	mW
50% Power Angle	201/2	I _F =700mA	-	140	-	deg

Note: Don't drive at rated current more than 5s without heat sink for Xeon 1 emitter series.

LED & Application Technologies





(Ta=25°C)







http://www.optosupply.com

VER A.0

^{*}Pulse width Max.10ms Duty ratio max 1/10



Xeon 3 Power Violet LED

OSV3XME3E1E

Ver.a.0

■ Handling of Silicone Lens LEDs

Notes for handling of silicone lens LEDs

- Please do not use a force of over 3kgf impact or pressure on the silicone lens, otherwise it will cause a catastrophic failure.
- The LEDs should only be picked up by making contact with the sides of the LED body.
- Avoid touching the silicone lens especially by sharp tools such as Tweezers.
- Avoid leaving fingerprints on the silicone lens.
- Please store the LEDs away from dusty areas or seal the product against dust.
- When populating boards in SMT production, there are basically no restrictions regarding the form of the pick and place nozzle, except that mechanical pressure on the silicone lens must be prevented.
- Please do not mold over the silicone lens with another resin. (epoxy, urethane, etc)



